

REF · WEB270

Alcalino

Alcalino - Non-foaming detergent for aluminum



DESCRIPTION

Non-foaming detergent with corrosion inhibitors. It can be used with aluminium utensils. Suitable for the automatic cleaning of utensils, trays, etc. It can also be used for the cleaning of tetrabrik packaging machines and floors with floor-cleaning machines.

DOSAGE AND USE INSTRUCTIONS

Dosage ranges from 1 to 4 %, at a max. temperature of 60°C.

TECHNICAL DATA

Appearance	Transparent clear brown liquid.
pH (1%)	12.0 +/- 0.5
Density (20°C)	1.17 +/- 0.02 g/ml

MAIN COMPONENTS

Contains phosphonates < 5 %, phosphates 5-15 %. Sodium hydroxide, potassium hydroxide.

PRESENTATION

24 kg.

USE OR HANDLING PRECAUTIONS

DANGER UN No.: UN3266



	DO NOT SWALLOW
H290	May be corrosive to metals.
H314	Causes severe skin burns and eye damage.
P102	Keep out of reach of children.
P280C	Wear protective gloves, clothing and eye protection.
P363	Wash contaminated clothing before reuse.
P301+P330+P331	IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
P303+P361+P353	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310	Immediately call a POISON CENTER or doctor.
P321	Specific treatment.
P501b	Dispose of contents/container to hazardous or special waste collection point.
	Do not mix with other chemicals.

Consult the Safety Data Sheet (SDS) before using the product.

MANUFACTURER

Detervic S.A.

Polígon Industrial Can Malloles · Sant Llorenç Desmunts, 32
08500 Vic · Barcelona

ES · CA · EN · FR · PT

DOCUMENT CONTROL

Rev. 2
Issued: 03/06/2024
Page 1 / 2

SALES CONTACT

T. +34 938 891 344
info@instaquim.com
instaquim.com

